

---

Item no.: 2002-1207  
Product description: 2-CONDUCTOR GROUND TERMINAL BLOCK SUITABLE FOR EX E APPLICATIONS

---



Produkt kann von Bild abweichen / product may differ

Packing unit 100 pieces

RoHS compliant

Product group	22 (TOPJOB S RAIL-MOUNTED TERMINAL BLOCKS)
Cross section [mm <sup>2</sup> ]	0.25 - 2.5 mm <sup>2</sup>
Cross section [AWG]	22 - 12 AWG
Connection method	CAGE CLAMP®S Connection
Cross section [mm <sup>2</sup> ]	0.25 - 4 mm <sup>2</sup>
Cross section [AWG]	22 - 12 AWG
Wiring method	e+f
Connection method	CAGE CLAMP®S Connection
Weight	7.555 g
Color	green-yellow
Wiring type	Front-entry
No. of connection Points	2
No. of potentials	1
Height	33 mm
Height	1.299 in
Width	5.2 mm
Width	0.205 in
Depth	48.5 mm

Depth	1.909 in
Strip length from	10 mm
Strip length to	12 mm
Strip length	0.43 in



Customs Tariff No.  
Country of Origin  
Mounting

85369010  
Deutschland  
TS 35



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [ mm <sup>2</sup> ]
2002-1207	ABS	05-HG476175/3-PDA			0,5-4
2002-1207	AEX	E185892			22-12
2002-1207	CCA	NL6387			0,2-2,5/4
2002-1207	CSA	154112-1536069			22-12
2002-1207	DNV	E-10423			0,5-4
2002-1207	GL	26187-05HH			0,25-2,5
2002-1207	KEMA	NL2116586.02			0,5-4
2002-1207	LR	91/20112(E6)			0,5-4
2002-1207	PRS	TE/1718/880590/08			0,2-4
2002-1207	PTB	IECEXPTB03.0004U			0,2-4
2002-1207	PTB	PTB03Atex1162U			0,2-4
2002-1207	RosTest	8189158			0,2-4
2002-1207	UR	E45172			22-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected