
Item no.: 2091-1106/002-000
Product description: Cable bundle function and unlocking aid 6 POLE PIN
SPACING 3.5 MM / 0.138 IN

Produkt kann von Bild abweichen / product may differ

RoHS compliant

Color	light gray
No. of connection Points	6
No. of potentials	6
pole count	6
Height	34 mm
Height	1.339 in
Width	21 mm
Width	0.827 in
Depth	12.4 mm
Depth	0.488 in
Pin spacing from	3.5 mm
Pin spacing from	0.138 in
Pollution degree	2
Measured voltage EN	160 V
Measured shock voltage	2.5 kV
Current intensity EN	10 A
Pollution degree	2
Measured voltage EN	320 V
Measured shock voltage	2.5 kV

Current intensity EN
Connection method
Cross section [mm²]

10 A
CAGE CLAMP®S Connection
0.2 - 1.5 mm²



Wiring method	solid
Cross section [mm ²]	0.2 - 1.5 mm ²
Cross section [mm ²]	0.25 - 0.75 mm ²
Cross section [mm ²]	0.25 - 1.5 mm ²
Cross section [AWG]	24 - 14 AWG
Strip length from	8 mm
Strip length to	9 mm
Material group	I
Customs Tariff No.	85366990

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected