

Data Sheet | Item Number: 211-500

Shrink tube; for Smart Printer; Unshrunk diameter: 2.4 mm; white

<https://www.wago.com/211-500>



Color: ■ white

Similar to illustration

Technical data

Suitable	for wire cross-section 0.25 ... 0.75 mm ²
Marking method	Thermal transfer
Delivery form	Roll
Delivery form configuration	20 m/roll
Printing device	Smart Printer (thermal transfer printer)

Physical data

Depth	0.185 mm
Sheathed cable diameter	2.4 mm

Mechanical data

Mounting type	Sliding on conductor
Shrink rate	2:1
Smear resistance	in conjunction with 258-5005 Ink Ribbon

Material data

Color	white
Material	Polyolefin
UV resistance	EN 60068-2-5:2010 Procedure B
Adhesive information	without adhesive
Halogen-free	Yes
Weight	141 g
Fire load	0 MJ

Environmental requirements

Ambient temperature (storage)	+10 ... +25 °C
Ambient temperature (operation)	-55 ... +125 °C
Relative humidity	45 ... 55 %

Commercial data

eCl@ss 10.0	27-40-04-01
eCl@ss 9.0	27-40-04-01
ETIM 8.0	EC001530
ETIM 7.0	EC001530
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	DK
GTIN	4055143370202
Customs tariff number	39173200910

Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

Downloads

Environmental Product Compliance


Compliance Search

Environmental Product
Compliance 211-500



Documentation

Operating Instructions

211-502 Information on printing material	1 28.08.2020	pdf 1059.74 KB	
---	-----------------	-------------------	---

1 Compatible Products

1.1 Optional Accessories

1.1.1 Marking

1.1.1.1 Marking device



Item No.: 258-5000

Thermal transfer printer; Smart Printer; for complete control cabinet marking; 300 dpi; With marking material