

## Data Sheet | Item Number: 211-504

Shrink tube; for Smart Printer; Unshrunk diameter: 9.5 mm; white

<https://www.wago.com/211-504>



Color: ■ white

Similar to illustration

### Technical data

Suitable	for wire cross-section 10 ... 16 mm <sup>2</sup>
Marking method	Thermal transfer
Delivery form	Roll
Delivery form configuration	15 m/roll
Printing device	Smart Printer (thermal transfer printer)

### Physical data

Depth	0.185 mm
Sheathed cable diameter	9.5 mm

### Mechanical data

Mounting type	Sliding on conductor
Shrink rate	2:1
Smear resistance	in conjunction with 258-5005 Ink Ribbon

### Material data

Color	white
Material	Polyolefin
UV resistance	EN 60068-2-5:2010 Procedure B
Adhesive information	without adhesive
Halogen-free	Yes
Weight	328.3 g
Fire load	0 MJ

### Environmental requirements

Ambient temperature (storage)	+10 ... +25 °C
Ambient temperature (operation)	-55 ... +125 °C
Relative humidity	45 ... 55 %

### Commercial data

eCl@ss 10.0	27-40-04-01
eCl@ss 9.0	27-40-04-01
ETIM 8.0	EC001530
ETIM 7.0	EC001530
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	DK
GTIN	4055143370295
Customs tariff number	39173200910

### Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

### Downloads

#### Environmental Product Compliance


##### Compliance Search

Environmental Product  
Compliance 211-504



### Documentation

#### Operating Instructions

211-502 Information on printing material	1 28.08.2020	pdf 1059.74 KB	
---	-----------------	-------------------	---

### 1 Compatible Products

#### 1.1 Optional Accessories

##### 1.1.1 Marking

###### 1.1.1.1 Marking device



##### Item No.: 258-5000

Thermal transfer printer; Smart Printer; for complete control cabinet marking; 300 dpi; With marking material