

Item no.: 2231-207/026-000  
 Product description: FEMALE CONNECTOR 7 POLE PIN SPACING 7.5 MM / 0.295 IN WITH CODING FINGERS WITH 2 LATCHES



Produkt kann von Bild abweichen / product may differ

Packing unit 50 pieces

RoHS compliant

Weight	13.95 g
Color	gray
No. of connection Points	7
No. of potentials	7
pole count	7
Height	15 mm
Height	0.591 in
Width	51.5 mm
Width	2.028 in
Depth	25.6 mm
Depth	1.008 in
Pin spacing from	7.5 mm
Pin spacing from	0.295 in
Pollution degree	2
Measured voltage EN	630 V
Measured shock voltage	6 kV
Current intensity EN	16 A
Pollution degree	2
Measured voltage EN	1000 V

Measured shock voltage  
Current intensity EN  
Connection method

6 kV  
16 A  
CAGE CLAMP®S Connection



Cross section [mm <sup>2</sup> ]	0.2 - 2.5 mm <sup>2</sup>
Wiring method	solid
Cross section [mm <sup>2</sup> ]	0.2 - 2.5 mm <sup>2</sup>
Cross section [mm <sup>2</sup> ]	0.25 - 1.5 mm <sup>2</sup>
Cross section [mm <sup>2</sup> ]	0.25 - 2.5 mm <sup>2</sup>
Cross section [AWG]	24 - 12 AWG
Strip length from	10 mm
Strip length to	11 mm
Material group	I
Customs Tariff No.	85366990
Country of Origin	Deutschland

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected