

Item no.: 2231-306/102-000
 Product description: FEMALE CONNECTOR WITH INTEGRATED END PLATE 6
 POLE PIN SPACING 5.08 MM / 0.2 IN WITH CODING
 FINGERS WITH 2 LATCHES



Produkt kann von Bild abweichen / product may differ

Packing unit 50 pieces

RoHS compliant

Weight	9.59 g
Color	orange
No. of connection Points	6
No. of potentials	6
pole count	6
Height	15 mm
Height	0.591 in
Width	30.48 mm
Width	1.2 in
Depth	25.6 mm
Depth	1.008 in
Pin spacing from	5.08 mm
Pin spacing from	0.2 in
Pollution degree	2
Measured voltage EN	320 V
Measured shock voltage	4 kV
Current intensity EN	16 A
Pollution degree	2

Measured voltage EN	630 V
Measured shock voltage	4 kV
Current intensity EN	16 A
Connection method	CAGE CLAMP®S Connection



Cross section [mm ²]	0.2 - 2.5 mm ²
Wiring method	solid
Cross section [mm ²]	0.2 - 2.5 mm ²
Cross section [mm ²]	0.25 - 1.5 mm ²
Cross section [mm ²]	0.25 - 2.5 mm ²
Cross section [AWG]	24 - 12 AWG
Strip length from	10 mm
Strip length to	11 mm
Material group	I
Customs Tariff No.	85366990
Country of Origin	Deutschland

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected