


Item no.: 231-102/026-000  
 Product description: FEMALE CONNECTOR 2 POLE PIN SPACING 5 MM / 0.197 IN WITH CODING FINGERS CLOSED END



Produkt kann von Bild abweichen / product may differ

Packing unit 200 pieces

RoHS compliant

Product group	3 (Multi Conn. System)
Weight	3.81 g
Color	gray
No. of connection Points	2
No. of potentials	2
pole count	2
Height	14.3 mm
Height	0.563 in
Width	11.5 mm
Width	0.453 in
Depth	26.45 mm
Depth	1.041 in
Pin spacing from	5 mm
Pin spacing from	0.197 in
Pollution degree	2
Measured voltage EN	320 V
Measured shock voltage	4 kV
Current intensity EN	16 A
Pollution degree	2

Measured voltage EN	630 V
Measured shock voltage	4 kV
Current intensity EN	16 A



Connection method	CAGE CLAMP® CONNECTION
Cross section [mm <sup>2</sup> ]	0.08 - 2.5 mm <sup>2</sup>
Wiring method	solid
Cross section [mm <sup>2</sup> ]	0.08 - 2.5 mm <sup>2</sup>
Cross section [mm <sup>2</sup> ]	0.25 - 1.5 mm <sup>2</sup>
Cross section [mm <sup>2</sup> ]	0.25 - 2.5 mm <sup>2</sup>
Cross section [AWG]	28 - 12 AWG
Strip length from	8 mm
Strip length to	9 mm
Material group	I
xxx-xxx/032-000	Strain relief plate 11,5 mm



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [ mm <sup>2</sup> ]
231-102/026-000	ABS	04-HG469925/1-PDA	400	16	5,0
231-102/026-000	BV	11915/A0	400	16	2,5
231-102/026-000	CCA	5764	250	16	0,08-2,5
231-102/026-000	CSA	154112-1466354	300	15	22-12
231-102/026-000	GL	17296-00HH	400	16	5,0
231-102/026-000	KEMA	2083746.02	250	16	0,08-2,5
231-102/026-000	KR	HMB05880-EL003	250/400	12/16	2,5
231-102/026-000	RMR	11130002	400	16	5,0
231-102/026-000	UR	E45171	600	15	28-12
231-102/026-000	UR	E45172	300	15	22-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected