



Product Number: 231-107/037-000
RoHS compliant

Packing unit 50 pieces

Product group	3 (Multi Conn. System)
Weight	12.72 g
Color	gray
No. of connection Points	7
No. of potentials	7
pole count	7
Height	14.3 mm
Height	0.563 in
Width	36.5 mm
Width	1.437 in
Depth	26.45 mm
Depth	1.041 in
Pin spacing from	5 mm
Pin spacing from	0.197 in
Pollution degree	2
Measured voltage EN	320 V
Measured shock voltage	4 kV
Current intensity EN	16 A
Pollution degree	2
Measured voltage EN	630 V
Measured shock voltage	4 kV
Current intensity EN	16 A
Connection method	CAGE CLAMP® CONNECTION
Cross section [mm ²]	0.08 - 2.5 mm ²
Wiring method	solid
Cross section [mm ²]	0.08 - 2.5 mm ²
Cross section [mm ²]	0.25 - 1.5 mm ²
Cross section [mm ²]	0.25 - 2.5 mm ²
Cross section [AWG]	28 - 12 AWG
Strip length from	8 mm
Strip length to	9 mm
Material group	I
xxx-xxx/034-000	Strain relief plate 30 mm

