



**Product Number:** 231-350/001-000

**HEADER STRAIGHT SOLDER PIN, 1X1 MM / 0.039X 0.039 IN 20 POLE PIN SPACING 5.08 MM / 0.2 IN MATING DIRECTION PERPENDICULAR TO PCB WITH CLOSED END**

**RoHS compliant**

Packing unit 50 5\*10 pieces

Product group	3 (Multi Conn. System)
Weight	6.51 g
Color	Orange
Pole Count	20
Height	12 mm (0.472 in)
Width	104.8 mm (4.126 in)
Depth	8.4 mm (0.331 in)
Pin spacing from	5.08 mm (0.2 in)
Pollution degree	2
Measured voltage EN	320 V
Measured shock voltage	2 kV
Current intensity EN	12 A
Pollution degree	2
Measured voltage EN	630 V
Measured shock voltage	4 kV
Current intensity EN	12 A
Material group	I
Contact surface	Tin-plated