


Item no.: 231-432/001-000/105-604
 Product description: HEADER RIGHT ANGLE SOLDER PIN, 1 X 1 MM / 0.039 X 0.039 IN 2 POLE PIN SPACING 5 MM / 0.197 IN SOLDER PIN LENGTH 2.4 MM WITH CLOSED END REFLOW TECHNIQUE MATING DIRECTION PARALLEL TO PCB



Produkt kann von Bild abweichen / product may differ

Packing unit 200 pieces

Weight	0.81 g
Color	black
pole count	2
Height	8.4 mm
Height	0.331 in
Width	13.2 mm
Width	0.52 in
Depth	12 mm
Depth	0.472 in
Pin spacing from	5 mm
Pin spacing from	0.197 in
Pollution degree	2
Measured voltage EN	320 V
Measured shock voltage	4 kV
Current intensity EN	12 A
Pollution degree	2
Measured voltage EN	320 V
Measured shock voltage	4 kV

Current intensity EN
Material group
Contact surface

12 A
I
tin-plated



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
231-432/001-000/105-604	CCA	5764	250	12	1x1
231-432/001-000/105-604	KEMA	2083746.02	250	12	1x1

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected