

**HEADER RIGHT ANGLE SOLDER PIN, 1 X 1 MM / 0.039 X 0.039 IN 10 POLE PIN SPACING 5.08 MM / 0.2 IN MATING DIRECTION PARALLEL TO PCB WITH CLOSED END**

Packing unit 100 4\*25 pieces

**RoHS compliant**

Product group	3 (Multi Conn. System)
Weight	3.39 g
Color	orange
pole count	10
Height	8.4 mm
Height	0.331 in
Width	54 mm
Width	2.126 in
Depth	12 mm
Depth	0.472 in
Pin spacing from	5.08 mm
Pin spacing from	0.2 in
Pollution degree	2
Measured voltage EN	320 V
Measured shock voltage	4 kV
Current intensity EN	16 A
Pollution degree	2
Measured voltage EN	630 V
Measured shock voltage	4 kV
Current intensity EN	16 A
Material group	I
Contact surface	tin-plated