


Item no.: 231-603/019-000
 Product description: MALE CONNECTOR WITH FIXING FLANGE 3 POLE PIN SPACING 5 MM / 0.197 IN FOR SCREW OR SIMILAR MOUNTING TYPES FOR PARALLEL OR PERPENDICULAR MOUNTING



Produkt kann von Bild abweichen / product may differ

Packing unit 50 pieces

Product group	3 (Multi Conn. System)
Weight	5.76 g
Color	gray
No. of connection Points	3
No. of potentials	3
pole count	3
Height	14.3 mm
Height	0.563 in
Width	29.8 mm
Width	1.173 in
Depth	27.5 mm
Depth	1.083 in
Pin spacing from	5 mm
Pin spacing from	0.197 in
Pollution degree	2
Measured voltage EN	320 V
Measured shock voltage	4 kV
Current intensity EN	12 A

Pollution degree	2
Measured voltage EN	630 V
Measured shock voltage	4 kV
Current intensity EN	12 A



Connection method	CAGE CLAMP® CONNECTION
Cross section [mm ²]	0.08 - 2.5 mm ²
Wiring method	solid
Cross section [mm ²]	0.08 - 2.5 mm ²
Wiring method	fine-stranded
Cross section [mm ²]	0.25 - 1.5 mm ²
Wiring method	fine-stranded (with ferrule and plastic collar)
Cross section [mm ²]	0.25 - 2.5 mm ²
Wiring method	fine-stranded (with ferrule, without plastic collar)
Cross section [AWG]	28 - 12 AWG
Strip length from	8 mm
Strip length to	9 mm
Material group	I
Contact surface	tin-plated
xxx-xxx/032-000	Strain relief plate 11,5 mm



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
231-603/019-000	ABS	04-HG469925/1-PDA	400	12	5,0
231-603/019-000	BV	11915/A0	400	16	2,5
231-603/019-000	CCA	5764	250	12	0,08-2,5
231-603/019-000	CSA	154112-1466354	300	15	22-12
231-603/019-000	GL	17296-00HH	400	12	5,0
231-603/019-000	KEMA	2083746.02	250	12	0,08-2,5
231-603/019-000	KR	HMB05880-EL003	250/400	12/16	2,5
231-603/019-000	LR	96/20035	400	12	5,0
231-603/019-000	RMR	11130002	400	12	5,0
231-603/019-000	UR	E45171	600	15	28-12
231-603/019-000	UR	E45172	300/150/300	15/15/10	22-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected