



Item no.: 231-635/017-000
 Product description: 1-CONDUCTOR-FEEDTHROUGH TERMINAL BLOCK RIGHT ANGLE CONNECTION PIN 1x1.2 MM 5 POLE WITH FIXING FLANGES FOR FEEDTHROUGHAPPLICATION PIN SPACING 5.08 MM / 0.2 IN



Produkt kann von Bild abweichen / product may differ

Packing unit 50 pieces

Product group	3 (Multi Conn. System)
Weight	7.33 g
Color	orange
No. of connection Points	5
No. of potentials	5
pole count	5
Height	14.3 mm
Height	0.563 in
Width	40.6 mm
Width	1.598 in
Depth	19.1 mm
Depth	0.752 in
Pin spacing from	5.08 mm
Pin spacing from	0.2 in
Pollution degree	2
Measured voltage EN	320 V
Measured shock voltage	4 kV
Current intensity EN	16 A

Pollution degree	2
Measured voltage EN	630 V
Measured shock voltage	4 kV
Current intensity EN	16 A



Connection method	CAGE CLAMP® CONNECTION
Cross section [mm ²]	0.08 - 2.5 mm ²
Wiring method	solid
Cross section [mm ²]	0.08 - 2.5 mm ²
Wiring method	fine-stranded
Cross section [mm ²]	0.25 - 1.5 mm ²
Wiring method	fine-stranded (with ferrule and plastic collar)
Cross section [mm ²]	0.25 - 2.5 mm ²
Wiring method	fine-stranded (with ferrule, without plastic collar)
Cross section [AWG]	28 - 14 AWG
Strip length from	8 mm
Strip length to	9 mm
Material group	I
Contact surface	tin-plated



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
231-635/017-000	ABS	04-HG469925/1-PDA	400	12	0,8-2,5
231-635/017-000	BV	11915/A0	400	16	2,5
231-635/017-000	CCA	5764	250	12	0,08-2,5
231-635/017-000	CSA	154112-1466354	300	15	22-12
231-635/017-000	GL	17296-00HH	400	12	0,8-2,5
231-635/017-000	KEMA	2083746.02	250	12	0,08-2,5
231-635/017-000	KR	HMB05880-EL003	250/400	12/16	2,5
231-635/017-000	LR	96/20035	400	12	0,8-2,5
231-635/017-000	RMR	11130002	400	12	0,8-2,5
231-635/017-000	UR	E45171	600	15	28-12
231-635/017-000	UR	E45172	300/150/300	15/15/10	22-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected