

Item no.: 233-103
 Product description: PCB TERMINAL STRIP 2 SOLDER PINS / POLE 3 POLE PIN
 SPACING 2.5 MM / 0.098 IN



Produkt kann von Bild abweichen / product may differ

Packing unit 500 4*125 pieces

Product group	4 (Printed Circuit)
Weight	1.123 g
Color	gray
No. of connection Points	3
No. of potentials	3
pole count	3
Height	11.7 mm
Height	0.461 in
Width	9.8 mm
Width	0.386 in
Depth	12.1 mm
Depth	0.476 in
Pin spacing from	2.5 mm
Pin spacing from	0.098 in
Pollution degree	2
Measured voltage EN	160 V
Measured shock voltage	2.5 kV
Current intensity EN	6 A
Pollution degree	2
Measured voltage EN	320 V

Measured shock voltage
Current intensity EN

2.5 kV
6 A



Connection method	CAGE CLAMP® CONNECTION
Cross section [mm ²]	0.08 - 0.5 mm ²
Wiring method	solid
Cross section [mm ²]	0.08 - 0.5 mm ²
Cross section to [mm ²]	0.25 mm ²
Cross section to [mm ²]	0.25 mm ²
Cross section [AWG]	28 - 20 AWG
Strip length from	5 mm
Strip length to	6 mm
Material group	I



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
233-103	ABS	04-HG469925/1-PDA	250	4	0,8-0,5
233-103	BV	11915/A0	250	6	0,08-0,5
233-103	CSA	154112-1465035	150	4	28-20
233-103	DEMKO	100741	130		0,08-0,5
233-103	DEMKO	DK96-03660	250	4	0,8-0,5
233-103	DNV	E-9215	250	4	0,8-0,5
233-103	GL	17296-00HH	250	4	0,8-0,5
233-103	KEMA	90.6212.01/02	250	6	0,08-0,5
233-103	RMR	11130002	250	4	0,8-0,5
233-103	SEMKO	9043004	250		0,5
233-103	UR	E45172	150	4	18-28

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected