


Item no.: 236-106  
 Product description: PCB TERMINAL STRIP 1 SOLDER PIN / POLE REAR 6 POLE  
 PIN SPACING 5/5.08 MM / 0.2 IN



Produkt kann von Bild abweichen / product may differ

Packing unit 140 4\*35 pieces

Product group	4 (Printed Circuit)
Weight	5.17 g
Color	gray
No. of connection Points	6
No. of potentials	6
pole count	6
Height	13 mm
Height	0.512 in
Width	32.3 mm
Width	1.272 in
Depth	14 mm
Depth	0.551 in
Pin spacing from	5 mm
Pin spacing up to	5.08 mm
Pin spacing from	0.197 in
Pin spacing up to	0.2 in
Pollution degree	2
Measured voltage EN	320 V
Measured shock voltage	4 kV
Current intensity EN	24 A

Pollution degree  
Measured voltage EN

2  
630 V



Measured shock voltage	4 kV
Current intensity EN	24 A
Connection method	CAGE CLAMP® CONNECTION
Cross section [mm²]	0.08 - 2.5 mm²
Wiring method	solid
Cross section [mm²]	0.08 - 2.5 mm²
Cross section [mm²]	0.25 - 1.5 mm²
Cross section [mm²]	0.25 - 1.5 mm²
Cross section [AWG]	28 - 12 AWG
Strip length from	5 mm
Strip length to	6 mm
Material group	I
xxx-xxx/000-004	black
xxx-xxx/000-006	blue
xxx-xxx/000-008	dark gray
xxx-xxx/000-009	light gray
xxx-xxx/000-012	orange
xxx-xxx/000-017	light green
xxx-xxx/000-023	green
xxx-xxx/332-xxx	with 2 solder pins/pole and 5,5 mm long solder pins
xxx-xxx/334-000	with 2 solder pins/pole and 3,6 mm long solder pins



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [ mm <sup>2</sup> ]
236-106	BV	11915/BO	500/250	16	0,08-2,5
236-106	CCA	NL6247	250	24	0,08-2,5
236-106	CSA	154112-1673957	300	15	28-12
236-106	DNV	E-9215	250	16	0,5-2,5
236-106	GL	17296-00HH	500/250	16	0,5-2,5
236-106	KEMA	2110204.01	250	24	0,08-2,5
236-106	NEMKO	M58459/01	50		2,5
236-106	RMR	11130002	250	16	0,5-2,5
236-106	SEMKO	9411003	400		2,5
236-106	UR	E45172	300/300	15/10	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected