

Item no.: 250-1405
 Product description: 1-CONDUCTOR PCB TERMINAL STRIP 1 SOLDER PIN /
 POLE STAGGERED 5 POLE PIN SPACING 2.54 MM / 0.1 IN
 WITH PUSH BUTTONS WITH TEST SLOT FOR TEST PLUG
 TO 1.3 MM Ø



Produkt kann von Bild abweichen / product may differ

Packing unit 240 4*60 pieces

| | |
|--------------------------|---------------------|
| Product group | 4 (Printed Circuit) |
| Weight | 1.92 g |
| Color | gray |
| No. of connection Points | 5 |
| No. of potentials | 5 |
| pole count | 5 |
| Height | 13.1 mm |
| Height | 0.516 in |
| Width | 14.2 mm |
| Width | 0.559 in |
| Depth | 12 mm |
| Depth | 0.472 in |
| Pin spacing from | 2.54 mm |
| Pin spacing from | 0.1 in |
| Pollution degree | 2 |
| Measured voltage EN | 160 V |
| Measured shock voltage | 2.5 kV |
| Current intensity EN | 4 A |

| | |
|------------------------|--------|
| Pollution degree | 2 |
| Measured voltage EN | 320 V |
| Measured shock voltage | 2.5 kV |
| Current intensity EN | 4 A |



| | |
|-------------------------------------|--|
| Diameter from | 0.4 mm |
| Diameter to | 0.8 mm |
| Cross section [mm ²] | 0.14 - 0.5 mm ² |
| Wiring method | solid |
| Cross section [mm ²] | 0.2 - 0.5 mm ² |
| Wiring method | fine-stranded |
| Cross section to [mm ²] | 0.25 mm ² |
| Wiring method | fine-stranded (with ferrule and plastic collar) |
| Cross section to [mm ²] | 0.25 mm ² |
| Wiring method | fine-stranded (with ferrule, without plastic collar) |
| Cross section [AWG] | 24 - 20 AWG |
| Strip length from | 8.5 mm |
| Strip length to | 9.5 mm |
| Material group | I |
| Contact surface | Copper |
| xxx-xxx/000-004 | black |
| xxx-xxx/000-005 | red |
| xxx-xxx/000-006 | blue |
| xxx-xxx/000-009 | light gray |
| xxx-xxx/000-012 | orange |
| xxx-xxx/000-024 | violet |
| xxx-xxx/000-050 | white |



| Item no. | Admission office | Approval no. | Voltage [V] | Current [A] | Cross section [mm ²] |
|----------|------------------|----------------|-------------|-------------|-----------------------------------|
| 250-1405 | CCA | NL6336 | 250 | 6 | 0,2-1,5 |
| 250-1405 | CSA | 154112-1132097 | 300 | 2 | 24-22 |
| 250-1405 | KEMA | 2114919.01 | 250 | 6 | 0,2-1,5 |
| 250-1405 | UR | E45172 | 300/300 | 5/5 | 26-20 |

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected