

---

Item no.: 264-724  
Product description: 4-CONDUCTOR MINIATURE THROUGH TERMINAL BLOCK  
SUITABLE FOR EX I APPLICATIONS

---



Produkt kann von Bild abweichen / product may differ

Packing unit 100 pieces

RoHS compliant

Product group	9 (Std Chassis Mt Blocks)
Cross section [mm <sup>2</sup> ]	0.08 - 2.5 mm <sup>2</sup>
Cross section [AWG]	28 - 12 AWG
Connection method	CAGE CLAMP® CONNECTION
Number of strands	2
Measured voltage EN	800 V
Measured shock voltage	8 kV
Pollution degree	3
Current intensity EN	24 A
Weight	6 g
Color	blue
Wiring type	Front-entry
No. of connection Points	4
No. of potentials	1
Height	24.5 mm
Height	0.96 in
Width	10 mm
Width	0.394 in
Depth	32 mm

Depth	1.26 in
Strip length from	8 mm
Strip length to	9 mm
Strip length	0.33 in
Mounting	TS15



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [ mm <sup>2</sup> ]
264-724	ABS	04-HG476174/1-PDA	800	24	2,5
264-724	BV	07436/C0			0,08-2,5
264-724	CSA	18677-23	600	20	26-12
264-724	DNV	E-9215	800	24	2,5
264-724	GL	17295-00HH	800	24	4
264-724	KR	HMB05880-EL002	800	24	
264-724	LR	92/20242(E5)	800	24	2,5
264-724	PRS	TE/1718/880590/08	800		2,5
264-724	RMR	11130002	800	24	2,5
264-724	UR	E45172	300	20	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected