



**Product Number: 2716-107**

**PCB TERMINAL STRIP 4 SOLDER PINS/POLE 7 POLE  
PIN SPACING 10 MM / 0.394 IN WITH LEVERS without jumper slot**

**RoHS compliant**

Packing unit 1 piece

Weight	65.13 g
Color	gray
No. of connection Points	7
No. of potentials	7
pole count	7
Height	28.8 mm
Height	1.134 in
Width	71.5 mm
Width	2.815 in
Depth	30 mm
Depth	1.181 in
Pin spacing from	10 mm
Pin spacing from	0.394 in
Pollution degree	2
Measured voltage EN	320 V
Measured shock voltage	4 kV
Current intensity EN	76 A
Pollution degree	2
Measured voltage EN	630 V
Measured shock voltage	4 kV
Current intensity EN	76 A
Connection method	CAGE CLAMP® CONNECTION
Cross section [mm <sup>2</sup> ]	1.5 - 16 mm <sup>2</sup>
Wiring method	solid
Cross section [mm <sup>2</sup> ]	1.5 - 16 mm <sup>2</sup>
Cross section [mm <sup>2</sup> ]	1.5 - 10 mm <sup>2</sup>
Cross section [mm <sup>2</sup> ]	1.5 - 10 mm <sup>2</sup>
Cross section [AWG]	16 - 6 AWG
Strip length from	12 mm
Strip length to	13 mm
Material group	I
Customs Tariff No.	85369010
Country of Origin	Schweiz
xxx-xxx/000-006	blue
xxx-xxx/000-009	light gray
xxx-xxx/000-016	green-yellow
xxx-xxx/000-017	light green