



Product Number: 2734-104

FEMALE CONNECTOR 4 POLE PIN SPACING 3.5 MM / 0.138 IN 100% PROTECTED AGAINST MISMATING WITH CODING FINGERS

RoHS compliant

Packing unit 100 pieces

Connection method	CONTACT CAGE CLAMP® CONNECTION
Weight	3.71 g
Color	light gray
No. of connection Points	4
No. of potentials	4
pole count	4
Height	13.5 mm
Height	0.531 in
Width	16.1 mm
Width	0.634 in
Depth	20.4 mm
Depth	0.803 in
Pin spacing from	3.5 mm
Pin spacing from	0.138 in
Pollution degree	2
Measured voltage EN	160 V
Measured shock voltage	2.5 kV
Current intensity EN	10 A
Pollution degree	2
Measured voltage EN	320 V
Measured shock voltage	2.5 kV
Current intensity EN	10 A
Cross section [mm ²]	0.2 - 1.5 mm ²
Wiring method	solid
Cross section [mm ²]	0.2 - 1.5 mm ²
Cross section [mm ²]	0.25 - 0.75 mm ²
Cross section [mm ²]	0.25 - 1.5 mm ²
Cross section [AWG]	28 - 14 AWG
Strip length from	7 mm
Strip length to	8 mm
Material group	I
Customs Tariff No.	85366990
Country of Origin	Deutschland