

Item no.: 2734-116  
 Product description: FEMALE CONNECTOR 16 POLE PIN SPACING 3.5 MM / 0.138 IN 100% PROTECTED AGAINST MISMATING WITH CODING FINGERS



Produkt kann von Bild abweichen / product may differ

Packing unit 25 pieces

RoHS compliant

Connection method	CAGE CLAMP®S Connection
Weight	14.15 g
Color	light gray
No. of connection Points	16
No. of potentials	16
pole count	16
Height	13.5 mm
Height	0.531 in
Width	58.1 mm
Width	2.287 in
Depth	20.4 mm
Depth	0.803 in
Pin spacing from	3.5 mm
Pin spacing from	0.138 in
Pollution degree	2
Measured voltage EN	160 V
Measured shock voltage	2.5 kV
Current intensity EN	10 A

Pollution degree	2
Measured voltage EN	320 V
Measured shock voltage	2.5 kV
Current intensity EN	10 A



Cross section [mm <sup>2</sup> ]	0.2 - 1.5 mm <sup>2</sup>
Wiring method	solid
Cross section [mm <sup>2</sup> ]	0.2 - 1.5 mm <sup>2</sup>
Cross section [mm <sup>2</sup> ]	0.25 - 0.75 mm <sup>2</sup>
Cross section [mm <sup>2</sup> ]	0.25 - 1.5 mm <sup>2</sup>
Cross section [AWG]	28 - 14 AWG
Strip length from	7 mm
Strip length to	8 mm
Material group	I
Customs Tariff No.	85366990
Country of Origin	Deutschland

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected