
Item no.: 282-607
Product description: 2-CONDUCTOR GROUND TERMINAL BLOCK



Produkt kann von Bild abweichen / product may differ

Packing unit 50 pieces

RoHS compliant

| | |
|----------------------------------|----------------------------------|
| Product group | 1 (Rail Mounted Terminal Blocks) |
| Cross section [mm ²] | 0.2 - 6 mm ² |
| Cross section [AWG] | 24 - 10 AWG |
| Connection method | CAGE CLAMP® CONNECTION |
| Weight | 19.732 g |
| Color | green-yellow |
| Wiring type | Front-entry |
| No. of connection Points | 2 |
| No. of potentials | 1 |
| Height | 31.5 mm |
| Height | 1.24 in |
| Width | 8 mm |
| Width | 0.315 in |
| Depth | 62 mm |
| Depth | 2.44 in |
| Strip length from | 12 mm |
| Strip length to | 13 mm |
| Strip length | 0.49 in |
| Mounting | TS 35 |



| Item no. | Admission office | Approval no. | Voltage [V] | Current [A] | Cross section [mm ²] |
|----------|------------------|-------------------|-------------|-------------|-----------------------------------|
| 282-607 | ABS | 05-HG476175/3-PDA | | | 6,0 |
| 282-607 | BV | 07436/Co | 800 | 41 | 6,0 |
| 282-607 | CCA | NL5448 | | | 6 |
| 282-607 | CSA | 154112-1505033 | | | 24-10 |
| 282-607 | DNV | E-10423 | 800 | 41 | 6,0 |
| 282-607 | GL | 17295-00HH | | | 6 |
| 282-607 | KEMA | 2036290.01 | | | 6 |
| 282-607 | KR | HMB05880-EL001 | 500/800 | 10/46 | 6 |
| 282-607 | LR | 91/20112(E6) | 800 | 41 | 6,0 |
| 282-607 | PRS | TE/1718/880590/08 | | | 6 |
| 282-607 | RMR | 11130002 | 800 | 41 | 6,0 |
| 282-607 | UR | E45172 | | | 24-10 |

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected