
Item no.: 285-635
Product description: 2-CONDUCTOR THROUGH TERMINAL BLOCK WITH INTEGRATED END PLATE



Produkt kann von Bild abweichen / product may differ

Packing unit 15 pieces

RoHS compliant

Product group	1 (Rail Mounted Terminal Blocks)
Cross section [mm ²]	6 - 35 mm ²
Cross section [AWG]	8 - 2 AWG
Connection method	CAGE CLAMP® CONNECTION
Measured voltage EN	1000 V
Measured shock voltage	8 kV
Pollution degree	3
Current intensity EN	125 A
Weight	88 g
Color	gray
Wiring type	Front-entry
No. of connection Points	2
No. of potentials	1
Height	53 mm
Height	2.09 in
Width	16 mm
Width	0.63 in
Depth	100 mm
Depth	3.937 in

Strip length from
Strip length to
Strip length

23 mm
23 mm
0.91 in



Strip length from	16 mm
Strip length	0.63 in
Strip length to	16 mm
Mounting	TS 35



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
285-635	ABS	05-HG476175/3-PDA	1000	125	35,0
285-635	CCA	NL6390	1000	125	35
285-635	CSA	154112-1327714	600	120	4-3/0
285-635	KEMA	2116735.01	1000	125	35
285-635	PRS	TE/1718/880590/08	1000	125	35
285-635	RMR	11130002	1000	125	35,0
285-635	UR	E45172	600	115	10-2tr

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected