



**Product Number: 713-1105**

**FEMALE CONNECTOR 5X2 POLE PIN SPACING 3.5 MM / 0.138 IN 100% PROTECTED AGAINST MISMATING**

**RoHS compliant**

Packing unit 50 pieces

Weight	5.31 g
Color	black
No. of connection Points	10
No. of potentials	10
pole count	10
Height	18.8 mm
Height	0.74 in
Width	19 mm
Width	0.748 in
Depth	16 mm
Depth	0.63 in
Pin spacing from	3.5 mm
Pin spacing from	0.138 in
Pollution degree	2
Measured voltage EN	160 V
Measured shock voltage	2.5 kV
Current intensity EN	10 A
Pollution degree	2
Measured voltage EN	250 V
Measured shock voltage	2.5 kV
Current intensity EN	10 A
Connection method	CAGE CLAMP® CONNECTION
Cross section [mm <sup>2</sup> ]	0.08 - 1.5 mm <sup>2</sup>
Wiring method	solid
Cross section [mm <sup>2</sup> ]	0.08 - 1.5 mm <sup>2</sup>
Cross section [mm <sup>2</sup> ]	0.25 - 1 mm <sup>2</sup>
Cross section [mm <sup>2</sup> ]	0.25 - 1 mm <sup>2</sup>
Cross section [AWG]	28 - 16 AWG
Strip length from	6 mm
Strip length to	7 mm
Material group	II
Customs Tariff No.	85366990
Country of Origin	Deutschland