



Pollution degree	2
Measured voltage EN	1000 V
Measured shock voltage	6 kV
Current intensity EN	12 A
Material group	I
Contact material	Electrolytic copper (Ecu)
Contact surface	tin-plated



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [ mm <sup>2</sup> ]
721-837/001-000	ABS	04-HG469925/1-PDA	400	16	0,08-2,5
721-837/001-000	BV	11915/A0	400	12	
721-837/001-000	CCA	5764	400	12	1x1
721-837/001-000	CSA	154112-1466354	300	15	
721-837/001-000	DNV	E-9218	400	16	0,08-2,5
721-837/001-000	GL	17296-00HH	400	12	
721-837/001-000	KEMA	2083746.02	400	12	1x1
721-837/001-000	KR	HMB05880-EL003	250/400	12/16	2,5
721-837/001-000	LR	96/20035	400	16	0,08-2,5
721-837/001-000	RMR	11130002	400	16	0,08-2,5
721-837/001-000	UR	E45171	600	10	
721-837/001-000	UR	E45172	300	10	

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected