


Item no.: 733-104
 Product description: FEMALE CONNECTOR WITH CODING FINGERS 4 POLE
 PIN SPACING 2.5 MM / 0.098 IN 100% PROTECTED
 AGAINST MISMATING



Produkt kann von Bild abweichen / product may differ

Packing unit 200 pieces

Weight	1.833 g
Color	light gray
No. of connection Points	4
No. of potentials	4
pole count	4
Height	11.8 mm
Height	0.465 in
Width	12.5 mm
Width	0.492 in
Depth	17.1 mm
Depth	0.673 in
Pin spacing from	2.5 mm
Pin spacing from	0.098 in
Pollution degree	2
Measured voltage EN	160 V
Measured shock voltage	2.5 kV
Current intensity EN	6 A
Pollution degree	2
Measured voltage EN	320 V

Measured shock voltage
Current intensity EN
Connection method

2.5 kV
6 A
CAGE CLAMP® CONNECTION



Cross section [mm ²]	0.08 - 0.5 mm ²
Wiring method	solid
Cross section [mm ²]	0.08 - 0.5 mm ²
Wiring method	fine-stranded
Cross section [mm ²]	0.25 - 0.34 mm ²
Wiring method	fine-stranded (with ferrule and plastic collar)
Cross section [mm ²]	0.25 - 0.34 mm ²
Wiring method	fine-stranded (with ferrule, without plastic collar)
Cross section [AWG]	28 - 20 AWG
Strip length from	5 mm
Strip length to	6 mm
Material group	I
Contact surface	tin-plated
xxx-xxx/032-000	Strain relief plate 6 mm



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
733-104	ABS	04-HG469925/1-PDA	250	4	0,8-0,5
733-104	BV	11915/A0	250	4	0,8-0,5
733-104	CCA	NL5640	250	4	0,8-0,5
733-104	CSA	154112-1465035	150	4	28-20
733-104	DNV	E-9218	250	4	0,8-0,5
733-104	GL	17296-00HH	250	4	0,8-0,5
733-104	KEMA	2077592.01	250	4	0,8-0,5
733-104	LR	96/20035	250	6	0,8-0,5
733-104	RMR	11130002	250	4	0,8-0,5
733-104	UR	E45171	250	4	28-20
733-104	UR	E45172	150	4	28-20

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected