



**Product Number: 733-336**

**HEADER STRAIGHT SOLDER PIN0.8x0.8 MM 6 POLE PIN SPACING 2.5 MM / 0.098 IN 100% PROTECTED AGAINST MISMATING MATING DIRECTION PERPENDICULAR TO PCB WITH CLOSED END**

**RoHS compliant**

Packing unit 200 pieces

Weight	0.883 g
Color	light gray
pole count	6
Height	8.9 mm
Height	0.35 in
Width	17.5 mm
Width	0.689 in
Depth	7.8 mm
Depth	0.307 in
Pin spacing from	2.5 mm
Pin spacing from	0.098 in
Pollution degree	2
Measured voltage EN	160 V
Measured shock voltage	2.5 kV
Current intensity EN	6 A
Pollution degree	2
Measured voltage EN	320 V
Measured shock voltage	2.5 kV
Current intensity EN	6 A
Material group	I
Contact surface	tin-plated