

Item no.:	733-362
Product description:	HEADER RIGHT ANGLE SOLDER PIN 0.8x0.8 MM 2 POLE PIN SPACING 2.5 MM / 0.098 IN 100% PROTECTED AGAINST MISMATING MATING DIRECTION PARALLEL TO PCB WITH CLOSED END



Packing unit 200 pieces

Product group	3 (Multi Conn. System)
Pin spacing from	2.5 mm
Pin spacing from	0.098 in
pole count	2
Measured voltage EN	250 V
Measured shock voltage	2.5 kV
Pollution degree	2
Current intensity EN	4 A
Weight	0.404 g
Color	light gray
Height	7.8 mm
Height	0.307 in
Width	7.5 mm
Width	0.295 in
Depth	8.9 mm
Depth	0.35 in



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm²]
733-362	ABS	04-HG469925-PDA	250	4	28-20
733-362	BV	11915/A0	250	4	
733-362	CCA	NL5640	250	4	
733-362	CSA	154112-1465035	150	4	
733-362	DNV	E-9218	250	4	
733-362	GL	17296-00HH	250	4	
733-362	KEMA	2077592.01	250	4	
733-362	LR	96/20035	250	6	28-20
733-362	RMR	11130002	250	4	
733-362	UR	E45171	250	4	
733-362	UR	E45172	150	4	

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected