

Item no.: 734-234/100-000
 Product description: HEADER PRESS-IN PIN 0.6x0.6 MM 4 POLE PIN SPACING 3.81 MM / 0.15 IN 100% PROTECTED AGAINST MISMATING WITH CLOSED END FOR PRESSIN TECHNIQUE MATING DIRECTION PERPENDICULAR TO PCB



Produkt kann von Bild abweichen / product may differ

Packing unit 200 pieces

Weight	0.9 g
Color	orange
pole count	4
Height	10.3 mm
Height	0.406 in
Width	17.33 mm
Width	0.682 in
Depth	8.5 mm
Depth	0.335 in
Pin spacing from	3.81 mm
Pin spacing from	0.15 in
Pollution degree	2
Measured voltage EN	160 V
Measured shock voltage	2.5 kV
Current intensity EN	8 A
Pollution degree	2
Measured voltage EN	320 V
Measured shock voltage	2.5 kV

Current intensity EN	8 A
PressIn pin: Thickness B [mm]	1.2 mm
Material group	I
Contact surface	tin-plated



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
734-234/100-000	ABS	04-HG469925/1-PDA	250	10	0,5-1,5
734-234/100-000	CCA	NL5641	250	10	0,5-1,5
734-234/100-000	CSA	154112-1465035	300	10	28-14
734-234/100-000	KEMA	2077592.02	250	10	0,5-1,5
734-234/100-000	UR	E45171	250	10	28-14
734-234/100-000	UR	E45172	300/300	10/10	

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected