


Item no.: 734-303/019-000
 Product description: MALE CONNECTOR WITH FIXING FLANGE 3 POLE PIN SPACING 3.5 MM / 0.138 IN 100% PROTECTED AGAINST MISMATING FOR SCREW OR SIMILAR MOUNTING TYPES FOR PARALLEL OR PERPENDICULAR MOUNTING



Produkt kann von Bild abweichen / product may differ

Packing unit 100 pieces

RoHS compliant

Product group	3 (Multi Conn. System)
Weight	3.553 g
Color	light gray
No. of connection Points	3
No. of potentials	3
pole count	3
Height	13.4 mm
Height	0.528 in
Width	25.3 mm
Width	0.996 in
Depth	22.3 mm
Depth	0.878 in
Pin spacing from	3.5 mm
Pin spacing from	0.138 in
Pollution degree	2
Measured voltage EN	160 V
Measured shock voltage	2.5 kV

Current intensity EN	10 A
Pollution degree	2
Measured voltage EN	320 V
Measured shock voltage	2.5 kV
Current intensity EN	10 A



Connection method	CAGE CLAMP® CONNECTION
Cross section [mm ²]	0.08 - 1.5 mm ²
Wiring method	solid
Cross section [mm ²]	0.08 - 1.5 mm ²
Cross section [mm ²]	0.25 - 1.5 mm ²
Cross section [mm ²]	0.25 - 1.5 mm ²
Cross section [AWG]	28 - 14 AWG
Strip length from	6 mm
Strip length to	7 mm
Material group	I
xxx-xxx/032-000	Strain relief plate 6 mm



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
734-303/019-000	ABS	04-HG469925/1-PDA	250	10	0,5-1,5
734-303/019-000	CCA	NL5641	250	10	0,5-1,5
734-303/019-000	CSA	154112-1465035	300	10	28-14
734-303/019-000	KEMA	2077592.02	250	10	0,5-1,5
734-303/019-000	UR	E45171	250	10	28-14
734-303/019-000	UR	E45172	300	10	28-14

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected