

Item no.: 734-408/001-000  
 Product description: DOUBLE DECK HEADERS RIGHT ANGLE SOLDER PIN, 1 X  
 1 MM / 0.039 X 0.039 IN 8X2 POLE PIN SPACING 3.5 MM /  
 0.138 IN 100% PROTECTED AGAINST MISMATING MATING  
 DIRECTION PARALLEL TO PCB WITH SUPPORT



Produkt kann von Bild abweichen / product may differ

Packing unit 50 pieces

RoHS compliant

Product group	3 (Multi Conn. System)
Weight	8.966 g
Color	light gray
pole count	8
Height	23 mm
Height	0.906 in
Width	30.4 mm
Width	1.197 in
Depth	16.8 mm
Depth	0.661 in
Pin spacing from	3.5 mm
Pin spacing from	0.138 in
Pollution degree	2
Measured voltage EN	160 V
Measured shock voltage	2.5 kV
Current intensity EN	10 A
Pollution degree	2

Measured voltage EN	320 V
Measured shock voltage	2.5 kV
Current intensity EN	10 A
Material group	I
Contact material	Electrolytic copper (Ecu)
Contact surface	tin-plated



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [ mm <sup>2</sup> ]
734-408/001-000	ABS	04-HG469925/1-PDA	250	10	0,5-1,5
734-408/001-000	CCA	NL5641	250	10	0,5-1,5
734-408/001-000	CSA	154112-1465035	300	10	28-14
734-408/001-000	KEMA	2077592.02	250	10	0,5-1,5
734-408/001-000	UR	E45171	250	10	28-14
734-408/001-000	UR	E45172	300	10	

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected