

Item no.: 739-304/100-000
 Product description: PCB TERMINAL STRIP 1 PRESS-IN PIN / POLE 4 POLE PIN
 SPACING 3.5 MM / 0.138 IN FOR PRESSIN TECHNIQUE



Produkt kann von Bild abweichen / product may differ

Packing unit 300 4*75 pieces

Product group	4 (Printed Circuit)
Weight	2.647 g
Color	gray
No. of connection Points	4
No. of potentials	4
pole count	4
Height	12.3 mm
Height	0.184 in
Width	15.5 mm
Width	0.61 in
Depth	13.4 mm
Depth	0.528 in
Pin spacing from	3.5 mm
Pin spacing from	0.138 in
Pollution degree	2
Measured voltage EN	160 V
Measured shock voltage	2.5 kV
Current intensity EN	4 A
Pollution degree	2
Measured voltage EN	320 V

Measured shock voltage
Current intensity EN

2.5 kV
4 A



Connection method	CAGE CLAMP® CONNECTION
Cross section [mm ²]	0.08 - 1.5 mm ²
Wiring method	solid
Cross section [mm ²]	0.08 - 1.5 mm ²
Cross section [mm ²]	0.25 - 1 mm ²
Cross section [mm ²]	0.25 - 0.25 mm ²
Cross section [AWG]	28 - 14 AWG
Strip length from	5 mm
Strip length to	6 mm
Material group	I



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
739-304/100-000	CCA	NL6364	130	4	0,08-1,5
739-304/100-000	KEMA	2110204.18	130	4	0,08-1,5
739-304/100-000	UR	E45172	300/300	4/4	28-14

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected