



Color: ■ light gray

Technical data

Rated current	10 A
---------------	------

Connection data

Solid conductor	0.08 ... 2.5 mm ² / 28 ... 14 AWG
Fine-stranded conductor	0.08 ... 2.5 mm ² / 28 ... 14 AWG
Strip length	9 ... 10 mm / 0.35 ... 0.39 inches

Physical data

Width	12 mm / 0.472 inches
Depth	74.3 mm / 2.925 inches

Mechanical data

Pluggable connector	pluggable
---------------------	-----------

Material data

Color	light gray
Fire load	0.204 MJ
Weight	11.2 g

Environmental requirements

Ambient temperature (operation)	0 ... +55 °C
Ambient temperature (storage)	-25 ... +85 °C
Protection type	IP20

Commercial data	
Product Group	15 (I/O System)
eCl@ss 10.0	27-24-26-92
eCl@ss 9.0	27-24-26-92
ETIM 8.0	EC002584
ETIM 7.0	EC002584
PU (SPU)	25 (1) pcs
Packaging type	Box
Country of origin	CN
GTIN	4050821043928
Customs tariff number	85366990990

Environmental Product Compliance	
RoHS Compliance Status	Compliant, No Exemption

Approvals / Certificates

General approvals

Approval	Standard	Certificate Name
UL Underwriters Laboratories Inc.	UL 1059	E45172

Approvals for marine applications

Approval	Standard	Certificate Name
ABS American Bureau of Ship- ping	-	22-2219060
BSH Bundesamt fuer See- schiffahrt und Hydrogra- phie	-	1104
BV Bureau Veritas S.A.	-	13453/E0 BV
DNV DNV GL SE	DNV-CG-0339, Aug. 2021	TAA0000194
KR Korean Register of Ship- ping	-	KR HMB05880-AC001
LR Lloyds Register EMEA	-	LR22180952TA
PRS Polski Rejestr Statków	-	TE/1101/880590/23
RINA RINA Germany GmbH	-	ELE343521XG001

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product
Compliance 753-110



Documentation

Bid Text

753-110	09.01.2019	docx 13.23 KB	
753-110	19.02.2019	xml 2.99 KB	

CAD/CAE-Data

CAD data

2D/3D Models 753-110



CAE data

EPLAN Data Portal
753-110



WSCAD Universe
753-110



ZUKEN Portal 753-110

