

Item no.: 769-102/022-000  
 Product description: 1-CONDUCTOR FEMALE PLUG ANGLED FOR USE WITH RECEPTACLE TERMINAL BLOCKS OF SERIES 769 AND 870 OR MALE CONNECTORS WITH CODING FINGERS 2 POLE



Produkt kann von Bild abweichen / product may differ

Packing unit 50 pieces

Product group	18 (X-COM-SYSTEM)
pole count	2
Cross section [mm <sup>2</sup> ]	0.08 - 4 mm <sup>2</sup>
Cross section [AWG]	28 - 12 AWG
Connection method	CAGE CLAMP® CONNECTION
Measured voltage EN	500 V
Measured shock voltage	6 kV
Pollution degree	3
Current intensity EN	32 A
Weight	4.84 g
Color	gray
Wiring type	Angled Type
No. of connection Points	2
No. of potentials	2
Height	37.1 mm
Height	1.461 in
Width	10 mm
Width	0.394 in

Depth	26.5 mm
Depth	1.043 in
Strip length from	8 mm
Strip length to	9 mm
Strip length	0.33 in



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [ mm <sup>2</sup> ]
769-102/022-000	ABS	05-HG476175/3-PDA	500	32	4
769-102/022-000	CSA	154112-1101144	300	20	28-12
769-102/022-000	KEMA	2077750.01	500	32	4
769-102/022-000	UR	E45171	600	20	16-12
769-102/022-000	UR	E45172	300	20	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected