

Item no.: 769-103/022-000
 Product description: 1-CONDUCTOR ANGLED FEMALE PLUG FOR USE WITH RECEPTACLE TERMINAL BLOCKS OF SERIES 769 AND 870 OR MALE CONNECTORS 3 POLE WITH CODING FINGERS



Packing unit 50 pieces

Cross section [mm ²]	0.08 - 4 mm ²
Cross section [AWG]	28 - 12 AWG
Product group	18 (X-COM-SYSTEM)
pole count	3
Cross section [mm ²]	0.08 - 4 mm ²
Cross section [AWG]	28 - 12 AWG
Connection method	CAGE CLAMP® CONNECTION
Measured voltage EN	500 V
Measured shock voltage	6 kV
Pollution degree	3
Current intensity EN	32 A
Weight	5.2 g
Color	gray
Wiring type	Angled Type
No. of connection Points	3
No. of potentials	3
Height	37.1 mm
Height	1.461 in
Width	15 mm
Width	0.591 in
Depth	26.5 mm
Depth	1.043 in



Strip length from	8 mm
Strip length to	9 mm
Strip length	0.33 in



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
769-103/022-000	ABS	04-HG476175-PDA	500	32	4
769-103/022-000	CSA	154112-1101144	300/300/600	20/20/5	28-12
769-103/022-000	KEMA	2077750.01	500	32	4
769-103/022-000	LR	91/20112(E6)	500	16	4
769-103/022-000	RMR	11130002	500	16	4
769-103/022-000	UR	E45171	600	20	16-12
769-103/022-000	UR	E45172	300/300/600	20/20/5	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected