

Item no.: 769-107/021-000
 Product description: 1-CONDUCTOR FEMALE PLUG WITH LATERAL LOCKING LEVERS 7 POLE ONLY TO BE USED FOR MALE CONNECTORS WITH CODING FINGERS COMMONING POSSIBILITY WITH MINIATURE ADJACENT JUMPERS



Produkt kann von Bild abweichen / product may differ

Packing unit 25 pieces

Product group	18 (X-COM-SYSTEM)
pole count	7
Cross section [mm ²]	0.08 - 4 mm ²
Cross section [AWG]	28 - 12 AWG
Connection method	CAGE CLAMP® CONNECTION
Measured voltage EN	500 V
Measured shock voltage	6 kV
Pollution degree	3
Current intensity EN	32 A
Weight	25.912 g
Color	gray
Wiring type	Front-entry
No. of connection Points	7
No. of potentials	7
Height	45.2 mm
Height	1.78 in
Width	50.6 mm
Width	1.992 in

Depth	18.3 mm
Depth	0.72 in
Strip length from	8 mm
Strip length to	9 mm
Strip length	0.33 in



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
769-107/021-000	ABS	04-HG476175-PDA	500	32	4
769-107/021-000	CSA	154112-1101144	300/300/600	20/20/5	28-12
769-107/021-000	KEMA	2077750.01	500	32	4
769-107/021-000	UR	E45171	600	20	16-12
769-107/021-000	UR	E45172	300/300/600	20/20/5	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected