

Item no.: 769-110/022-000
 Product description: 1-CONDUCTOR ANGLED FEMALE PLUG FOR USE WITH RECEPTACLE TERMINAL BLOCKS OF SERIES 769 AND 870 OR MALE CONNECTORS 10 POLE WITH CODING FINGERS



Packing unit 50 pieces

Product group	18 (X-COM-SYSTEM)
pole count	10
Cross section [mm ²]	0.08 - 4 mm ²
Cross section [AWG]	28 - 12 AWG
Connection method	CAGE CLAMP® CONNECTION
Measured voltage EN	500 V
Measured shock voltage	6 kV
Pollution degree	3
Current intensity EN	32 A
Weight	23.9 g
Color	gray
Wiring type	Angled Type
No. of connection Points	10
No. of potentials	10
Height	37.1 mm
Height	1.461 in
Width	50 mm
Width	1.969 in
Depth	26.5 mm
Depth	1.043 in
Strip length from	8 mm
Strip length to	9 mm

Strip length

0.33 in



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
769-110/022-000	ABS	04-HG476175-PDA	500	32	4
769-110/022-000	CSA	154112-1101144	300/300/600	20/20/5	28-12
769-110/022-000	KEMA	2077750.01	500	32	4
769-110/022-000	UR	E45171	600	20	16-12
769-110/022-000	UR	E45172	300/300/600	20/20/5	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected