
Item no.: 770-112/041-000
Product description: PLUG WITH RELIEF HOUSING 2 POLE PIN SPACING 10 MM
/ 0.394 IN 100% PROTECTED AGAINST MISMATING Wire
diameter 7 - 10,5 mm



Produkt kann von Bild abweichen / product may differ

Packing unit 25 pieces

RoHS compliant

Product group	20 (WINSTA)
pole count	2
Cross section [mm ²]	0.5 - 4 mm ²
Cross section [AWG]	20 - 12 AWG
Connection method	CAGE CLAMP®S Connection
Measured voltage EN	250 V
Measured shock voltage	4 kV
Pollution degree	3
Current intensity EN	25 A
Color	black
No. of connection Points	4
No. of potentials	2
Height	15.9 mm
Height	0.626 in
Width	24.6 mm
Width	0.969 in
Depth	71 mm
Depth	2.795 in

Strip length from	9 mm
Strip length to	9 mm
Strip length	0.35 in

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected