
#### WALL-NUTS™

#### Connect Stranded and

#### Solid Wire

Fast - Safe - Easy



File: | R46759

600 V building wiring

1000 V fixtures and signs



Clear housing allows visual confirmation of connection Test port for easy continuity testing

File: E69654



WAGO Corporation N120 W19129 Freistadt Rd., P.O. Box 1015, Germantown, WI 53022 Tel.: 262 / 255-6222 Fax: 262 / 255-3232 Toll Free: 1-800-DIN RAIL (346-7245) www.wago.com info.us@wago.com



# WALL-NUTS™

### Pushwire Connectors

for solid and stranded copper wire



# Introducing WALL-NUTS<sup>TM</sup>

WALL-NUTS<sup>™</sup> are the first push-in connectors that connect both <u>stranded and solid copper</u> wires. Now you can use the speed and dependability of push-wire technology in every application.



## See The Safety

WALL-NUTS<sup>™</sup> clear housing means you can see the firm connection of solid or stranded conductors. No more guessing whether the wires are twisted together or are pushed

in far enough. Visual inspection allows you to see that WALL-NUTS<sup>™</sup> make reliable connections.

## Fast, Easy Installation

The new WALL-NUTS<sup>™</sup> push-in connectors makes the job of wire connecting easier. No more twisting and taping required. Simply strip the wire; insert the conductor and you're finished.



The integrated test port allows for continuity testing without reinsertion.

# Safe

WALL-NUTS<sup>™</sup> hold each wire individually, eliminating loose connections. WALL-NUTS<sup>™</sup> are touch-proof and rated to 105° C. WALL-NUTS<sup>™</sup> are UL Listed/CSA certified for 600 volts (1000 volts for fixtures and signs) and current rated to the largest conductor used.



WALL-NUTS<sup>™</sup> are perfect for new construction and retrofit work.



WALL-NUTS<sup>™</sup> work with solid and stranded wire making main, branch and fixture hookup fast, easy and safe.


### Save Time

WALL-NUTS<sup>™</sup> provide up to 50% time savings on installation. Secure connections reduce expensive trouble shooting and warranty work.

## 18 AWG Stranded Range

The 773-124 has a special opening that accepts 18 AWG stranded copper wire. This makes the connection of incandescent light fixtures, dimmer switches, ceiling fans and other accessories to branch and main circuits a breeze.

Toll Free: 1-800-DIN RAIL (346-7245)



WALL-NUTS™ The 773-124's special opening wire range 18 stranded or solid; 18-22 tinned stranded copper.