


Item no.: 831-3602
 Product description: HEADER WITH STRAIGHT SOLDER PIN 2 POLE PIN SPACING 7.62 MM / 0.3 IN 100% PROTECTED AGAINST MISMATING 3 x solder pins 1 mm x 1.2 mm MATING DIRECTION PERPENDICULAR TO PCB



Produkt kann von Bild abweichen / product may differ

Packing unit 1 piece

RoHS compliant

Weight	6.34 g
Color	light gray
pole count	2
Height	29 mm
Height	1.142 in
Width	18.12 mm
Width	0.713 in
Depth	14.8 mm
Depth	0.583 in
Pin spacing from	7.62 mm
Pin spacing from	0.3 in
Pollution degree	2
Measured voltage EN	630 V
Measured shock voltage	6 kV
Current intensity EN	41 A
Pollution degree	2
Measured voltage EN	1000 V

Measured shock voltage	6 kV
Current intensity EN	41 A
Material group	I
Contact material	Electrolytic copper (Ecu)
Contact surface	tin-plated
Customs Tariff No.	85366990



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
831-3602	CCA	NL6348	800	41	0,5-6
831-3602	CSA	154112-1466354	300	50	
831-3602	KEMA	NL2116213.01	800	41	0,5-6
831-3602	PSE	JET0695-43009-1003	300/600	42/5	
831-3602	UR	E45172	600	42	

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected