


Item no.: 862-1533/999-950
 Product description: 1 SNAP-IN FOOT PER POLE PE-N-L1 without ground contact
 SUITABLE FOR EX E APPLICATIONS 3 POLE



Produkt kann von Bild abweichen / product may differ

Packing unit 250 pieces

RoHS compliant

Weight	21.018 g
pole count	3
Cross section [mm ²]	0.5 - 4 mm ²
Cross section [AWG]	20 - 12 AWG
Height	21.4 mm
Height	0.843 in
Width	36 mm
Width	1.417 in
Depth	35 mm
Depth	1.378 in
Strip length from	10 mm
Strip length to	11 mm
Strip length	0.41 in
No. of connection Points	12
Measured voltage EN	440 V
Current intensity EN	28 A
Product group	9 (Std Chassis Mt Blocks)
Connection method	CAGE CLAMP®S Connection
Measured shock voltage	6 kV

Pollution degree	3
Color	black
No. of potentials	3
Customs Tariff No.	85369010
Country of Origin	Deutschland

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected