


Item no.: 862-2504
 Product description: 4-CONDUCTOR DEVICE CONNECTORS FOR TOP FIXING SCREWS AND NUTS 3 MM Ø OR FOR SELF-TAPPING SCREW 2.9 MM Ø N-PE-L1-L2 without ground contact 4 POLE



Produkt kann von Bild abweichen / product may differ

Packing unit 200 pieces

RoHS compliant

Product group	9 (Std Chassis Mt Blocks)
pole count	4
Cross section [mm ²]	0.5 - 4 mm ²
Cross section [AWG]	20 - 12 AWG
Connection method	CAGE CLAMP®S Connection
Measured voltage EN	500 V
Measured shock voltage	6 kV
Pollution degree	3
Current intensity EN	32 A
Weight	27.7 g
Color	black
No. of connection Points	16
No. of potentials	4
Height	22.3 mm
Height	0.878 in
Width	48 mm
Width	1.89 in
Depth	35 mm

Depth	1.378 in
Strip length from	10 mm
Strip length to	11 mm
Strip length	0.41 in



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
862-2504	CSA	154112-1505030	300	20	22-12
862-2504	DNV	E-10423	500	32	4,0
862-2504	ENEC15	143856-01	500	32	0,5-4
862-2504	GL	33242-06HH	500	32	4
862-2504	LR	91/20112(E6)	500	32	4,0
862-2504	LR	91/20112E4	500	32	4
862-2504	UR	E45172	300	20	22-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected