

Item no.: 862-505
 Product description: 4-CONDUCTOR DEVICE CONNECTORS FOR TOP FIXING
 SCREWS AND NUTS 3 MM Ø OR FOR SELF-TAPPING
 SCREW 2.9 MM Ø WITHOUT MARKING without ground contact
 5 POLE



Produkt kann von Bild abweichen / product may differ

Packing unit 200 pieces

RoHS compliant

Product group	9 (Std Chassis Mt Blocks)
pole count	5
Cross section [mm ²]	0.5 - 4 mm ²
Cross section [AWG]	20 - 12 AWG
Connection method	CAGE CLAMP®S Connection
Measured voltage EN	500 V
Measured shock voltage	6 kV
Pollution degree	3
Current intensity EN	32 A
Weight	34.07 g
Color	black
No. of connection Points	20
No. of potentials	5
Height	21.4 mm
Height	0.843 in
Width	60 mm
Width	2.362 in

Depth	35 mm
Depth	1.378 in
Strip length from	10 mm
Strip length to	11 mm
Strip length	0.41 in



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
862-505	CSA	154112-1505030	300	20	22-12
862-505	DNV	E-10423	500	32	4,0
862-505	ENEC15	143856-01	500	32	0,5-4
862-505	GL	33242-06HH	500	32	4
862-505	LR	91/20112(E6)	500	32	4,0
862-505	LR	91/20112E4	500	32	4
862-505	UR	E45172	300	20	22-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected