



Color: ■ gray

#### Notes

Safety Information

Push down the wire jumper until fully inserted!

#### Electrical data

##### Ratings per IEC/EN

Nominal voltage (III/3) 800 V

Rated impulse voltage (III / 3) 8 kV

Rated current 9 A

#### Connection data

##### Connection 1

Solid conductor 0.75 mm<sup>2</sup>

#### Mechanical data

Wire length of wire jumpers 60 mm

#### Material data

Note (material data)

[Information on material specifications can be found here](#)

Color

gray

Fire load

0.015 MJ

Weight

1.5 g

## Commercial data

Product Group	2 (Terminal Block Accessories)
eCl@ss 10.0	27-14-11-40
eCl@ss 9.0	27-14-11-40
ETIM 8.0	EC000489
ETIM 7.0	EC000489
PU (SPU)	100 (10) pcs
Packaging type	Box
Country of origin	DE
GTIN	4050821458883
Customs tariff number	85444290900

## Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

## Downloads

### Environmental Product Compliance

#### Compliance Search

Environmental Product  
Compliance 2009-402



## Documentation

### Additional Information

Technical Section

pdf  
2246.92 KB



### Bid Text

2009-402

19.02.2019

xml  
2.77 KB



2009-402

28.04.2017

doc  
23.50 KB



## CAD/CAE-Data

### CAE data

EPLAN Data Portal  
2009-402



WSCAD Universe  
2009-402



## Installation Notes

### Commoning



Push down the wire jumper (2009-402) until fully inserted. For rewiring, lift the jumper with an operating tool at the notch provided for this purpose on the jumper.

## Commoning



Push-in type wire jumpers common terminal blocks over longer distances and across multiple levels.