

Datasheet

Item No. 70.320.3228.0

Bottom BAS GUT GA 32 50 A

revos BASIC 500V size 32 open-bottom base, double locking lever



Item No.	70.320.3228.0
EAN	4015573220133
order unit	1 Piece(s)

Approvals



Technical data

General

Nominal voltage	500
Housing material	Aluminium
Colour	Grey
Surface	With powder coating
Degree of protection (IP)	IP54
UV resistant	Yes
Inflammability class of insulation material acc. with UL94	Other
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

Model

DIN-size	32
Model	Equipment mounted (feed-through)
Locking mechanism	Double locking levers
Cable entry	None
Type of cable	None
With cable screw gland	No
Hinged lid	No
EMC-version	No

Drawings

