

Datasheet

Item No. 70.354.1635.1

Hood BAS GOT GC 16 M32 50 A1

revos BASIC 500V size 16 hood with threaded collar M32, top cable entry, double locking lever



Item No.	70.354.1635.1
EAN	4015573650916
order unit	1 Piece(s)

Approvals



Technical data

General

Nominal voltage	500
Housing material	Aluminium
Colour	Grey
Surface	With powder coating
Degree of protection (IP)	Other
UV resistant	Yes
Inflammability class of insulation material acc. with UL94	Other
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

Model

DIN-size	16
Model	Plug
Locking mechanism	Double locking levers
Cable entry	Above
Type of cable	Thread
With cable screw gland	No
Thread size M	32
Hinged lid	No
EMC-version	No

Drawings

