

## Datasheet

Item No. 72.310.0653.0

Male insert BAS STS 6 2,5 69

revos BASIC 690V 6 pole + ground, male insert 690V/16A, screw connection



Item No.	72.310.0653.0
EAN	4015573227231
order unit	10 Piece(s)

### Approvals



### Technical data

#### General

ArticlePrice	udp_no_price
Model	Pin insert
Size (in accordance with DIN 43880)	6
Inflammability class of insulation material acc. with UL94	V0
Colour	Grey
Mating cycles	200
Pollution degree	3
Modular version	No
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

#### Connection Data

Connection type	Screw connection
Number of poles	4
Plus switching contacts	2
Number of pole for rated current 2	0
Number of pole for rated current 3	0
Total number of poles (without ground contact)	6
With wire protection	Yes
Min. conductor diameter rigid (solid/stranded)	0.5
Max. conductor diameter rigid (solid/stranded)	2.5
Protective contact	Yes

#### Technical Data UL/CSA

Rated voltage according to UL/CSA	600
Rated current according UL	5
Rated current according CSA	16
Min. conductor cross section flexible wire	0.5
Max. conductor cross section flexible wire	2.5
Conductor cross section flexible AWG wire	22-12 AWG

**Model**

With housing	No
--------------	----

**Contacts**

Contact material	Copper alloy
Surface	Tin-plated
Contact resistance	1.5 mOhm
Wire strip length	7 mm

**Screws head design/recomm. Torque**

Mounting screws	H1/0.5-0.7 Nm
Clamping screws	H1/0.5-0.7 Nm
Ground conductor screws	H2/1.2-1.6 Nm

**Technical Data DIN EN 61984**

Nominal voltage	690
Rated voltage face/ground	690
Nominal current	16
Rated impulse voltage	8 kV