

Datasheet

Item No. 80.010.1002.0

Relay module WRS-REL-2W-48V20M

WRS-relays, contact Assignment: 2 change-over contacts, gold-plated contact, relay not pluggable, with LED, open module housing WEB 1002, dimensions: 80x22,5mm (HxW), control voltage: 24V DC, output voltage: maximim 48VDC / 20mADC (Remark: the negative pole can be linked At the controll side with A jumper to the next module, if needed they have to be ordered seperately).



Item No.	80.010.1002.0
EAN	4015573322523
order unit	5 Piece(s)

Approvals



Technical data

General

ArticlePrice	udp_no_price
Connection type	Screw connection
Number of change-over contacts	2
Detachable clamps	No
Drive, polarization	Polarity free
Drive, function	Mono stable
Forced-guided contacts	No
Complete with socket	Yes
Degree of protection (IP)	IP20

Technical data

Rated frequency, auxiliary-/control circuit	50 - 60
Min. rated frequency, auxiliary/control current circuit	50 Hz
Max. rated frequency, auxiliary/control current circuit	60 Hz
Nominal voltage DC	24 V
Lower nominal voltage DC	20.4 V
Upper nominal voltage DC	26.4 V

Dimensions

Depth	60 mm
Width	22.5 mm

Height	80 mm
--------	-------