

Datasheet

Item No. 80.010.4100.0

Relay module FLARE-24DC-1W-250V6A-F

flare, mechanical relays with 6,2 mm overall width, output, 1 change-over contact, spring clamp terminal, input: 24 V DC, output: 250V AC / 6A, voltage / current minimum: 24V / 8mA, jumper At negative pole At the controll side , type: flare-24VDC-1W-250V6A-F



Item No.	80.010.4100.0
EAN	4015573431140
order unit	10 Piece(s)

Approvals



Technical data

**General**

ArticlePrice	udp_no_price
Connection type	Tension clamp connection
Number of change-over contacts	1
Detachable clamps	No
Drive, polarization	Polarity free
Drive, function	Mono stable
Forced-guided contacts	No
Complete with socket	Yes
Degree of protection (IP)	IP20

**Technical data**

Nominal voltage DC	24 V
Lower nominal voltage DC	19.2 V
Upper nominal voltage DC	30 V

**Dimensions**

Depth	70 mm
Width	6.2 mm
Height	98 mm