

Datasheet

Item No. 92.042.0058.1

Male connector GST18I4L S1V SW

Device connectors, PCB mount, GST18i4, 4 pole, vertical, male, 250/400V, 16A, color of coding: black



Item No.	92.042.0058.1
EAN	4015573459137
order unit	100 Piece(s)

Approvals



LR



Technical data

General

ArticlePrice	udp_no_price
Rated current	20 A
Rated voltage	400 V
Pollution degree	2
Mechanical coding	Yes
Rated impulse voltage	4 kV
Interlockable	Yes
Color of coding/ contact carrier	Black
Terminations per pole	1

Model

Model	Plug
Number of poles	4
Connection type	Soldering connection
Connecting thread metric	No thread
Angle of plug	Straight
Degree of protection (IP)	IP40
Built-in component	Soldering connection

Material

Housing material	Polyamide
Halogen free	Yes
Contact material	CuZn
Insulation components continuous temperature	100 °C

Surface finish	Tin-plated
Dimensions	
Length	24 mm
Width	38 mm
Height	13 mm

Drawings