

## Datasheet

Item No. 92.042.3353.1

### Male connector GST18I4S S1 SW

Device connectors, built-in components, GST18i4, 4 pole, female, screw connection, 250/400V, 16A, color of coding: black



Item No.	92.042.3353.1
EAN	4015573545946
order unit	100 Piece(s)

### Approvals



### Technical data

#### General

ArticlePrice	udp_no_price
Rated current	20 A
Rated voltage	400 V
Pollution degree	2
Mechanical coding	Yes
Rated impulse voltage	4 kV
Interlockable	Yes
Color of coding/ contact carrier	Black
Connection cross section solid	2.5 mm <sup>2</sup>
Cross section solid 2	0.5 mm <sup>2</sup>
Connection cross section stranded	2.5 mm <sup>2</sup>
Cross section stranded 2	0.5 mm <sup>2</sup>
Terminations per pole	1

#### Model

Model	Plug
Number of poles	4
Connection type	Screw connection
Connecting thread metric	M3
Angle of plug	Straight
Degree of protection (IP)	IP20
Built-in component	Built-in component/connector

#### Material

Housing material	Polyamide
Halogen free	Yes
Contact material	CuZn
Insulation components continuous temperature	100 °C
Surface finish	Tin-plated

**Dimensions**

Length	31.5 mm
Width	38 mm
Height	19.5 mm

## Drawings